

Abstract Submitted
for the MAR16 Meeting of
The American Physical Society

Electroabsorption spectroscopy of bulk heterojunction solar cells

MARIAN TZOLOV, ZANE COHICK, CHRISTOPHER GREEN, Lock Haven University of PA — Bulk heterojunction solar cells were fabricated using PCPDTBT polymer and PCBM in inert atmosphere. Electroabsorption (EA) spectroscopy was performed in the spectral range 350-1000 nm. The first derivative of the optical absorbance spectra explains satisfactory most of the bands in the EA spectra. The only deviation is in the spectral range around 760 nm. Control experiments with devices containing only a PCPDTBT film confirm that the band at 760 nm is associated with the presence of PCBM, despite that pristine PCBM is not expected to have such band. Electrical DC bias strongly affects this band. Negative DC bias almost completely eliminates this band, while positive bias enhances it. We interpret the band at 760 nm as due to photogenerated charge carriers trapped at defect states or at interfaces within the composite PCPDTBT/PCBM film. The effective transfer of photogenerated charge carriers between PCPDTBT and PCBM is confirmed by the quenching of the photoluminescence in the composite film, while the emission of electroluminescence from the devices confirms that PCPDTBT is an effective medium for recombination of charges injected in it.

Marian Tzolov
Lock Haven University of PA

Date submitted: 29 Oct 2015

Electronic form version 1.4